

MPI TS3500-IFE | 300 mm Automated Probe Systems

The Dedicated Systems for Product Engineering with IceFreeEnvironment™

FEATURES / BENEFITS

Designed for Variety of On-Wafer Applications

- DC-IV / DC-CV / Pulsed-IV applications
- RF, mmW, load-pull applications & 4-port setup
- IC Design Validation, Failure Analysis in wide temperature range from -60 to 300 °C
- Wafer Level Reliability

WaferWallet® Option

- Designed with five individual trays for manual, ergonomic loading of 150, 200, or 300 mm “modeling” wafers
- Fully-automated tests with up to five identical wafers at multiple temperatures
- Unique capability to load/unload wafers at any temperature

Extended Flexibility

- MPI IceFreeEnvironment™ for using MicroPositioners and probe cards simultaneously, even at negative temperature
- Programmable microscope movements for more automation and ease of use
- The shortest cable interface to IC tester
- Minimize the platen-to-chuck distance for mmW & probing with active probes
- Supports film-frame probing

Ergonomic Design and Footprint

- Easy wafer or single DUT loading from the front
- Integrated active vibration isolation
- Completely integrated prober control for faster, safer and convenient system and test operation
- The Safety Test Management (STM™) with automated dew point control
- Reduced footprint due to smart chiller space arrangement
- Instrument shelf option for shorter cables and higher measurement dynamic



STAGE SPECIFICATIONS

Chuck XY Stage (Programmable)

Travel range	310 mm x 530 mm (12.2 x 20.87 in)
Resolution	0.5 µm
Accuracy	< 2.0 µm (0.08 mils)
XY stage drive	Closed-loop high precision stepper motors
Speed	5-Speed XY chuck stage speed movement
Max. movement speed	50 mm / sec

Chuck Z Stage (Programmable)

Travel range	30 mm (1.18 in)
Resolution	0.2 µm
Accuracy	< 2 µm
Repeatability	< 1 µm
Z stage drive	Closed-loop high precision stepper motor
Guider	Precision ball bearings

■ STAGE SPECIFICATIONS

Chuck Theta Stage (Programmable)

Travel range	$\pm 5.0^\circ$
Resolution	0.0001° (0.24 μm @ 300 mm edge)
Accuracy	< 2.0 μm (measured at the edge of the 300 mm chuck)
Repeatability	< 1.0 μm
Theta stage drive	High resolution stepper motor with linear encoder feedback system

■ AUTOMATED WAFER LOADING OPTIONS

WaferWallet®



Wafer loading trays	5
Supported wafer sizes	150, 200, or 300 mm
Individual notch marks	0, 90, 180 & 270 deg for all wafer sizes
Hot and cold wafer swapping	Yes, local environmental chamber
Wafer pre-aligner	For 150, 200 and 300 mm, option
Wafer ID-Reader	Option for top or bottom ID reading Revolutionary integrated RGB illumination Fully automatic exposure control Code shift compensation OCR, Barcode, DataMatrix and QR code
Signal light tower	Four color, LED steady/flashing tower lights

WaferWallet®MAX



Number of cassettes	1
Cassette type	Semi Standard, opened
Supported wafer sizes	150, 200 or 300 mm FOUP/FOSB Semi standard opened cassette
Wafer pre-aligner	Included
Cassette scanner	Included
Wafer ID-Reader	Option for top or bottom ID reading Revolutionary integrated RGB illumination Fully automatic exposure control Code shift compensation OCR, Barcode, DataMatrix and QR code
Signal light tower	Four color, LED steady / flashing tower lights

WaferWallet®ULTRA



Load port	300 mm with automated door opener
Supported wafer size	300 mm FOUP cassette, 200 mm with insert adapter
Wafer pre-aligner	Included
Cassette scanner	Included
Wafer ID-Reader	Option for top or bottom ID reading Revolutionary integrated RGB illumination Fully automatic exposure control Code shift compensation OCR, Barcode, DataMatrix and QR code
Signal light tower	Four color, LED steady/flashing tower lights

MANUAL WAFER LOADING

Loading or unloading of 150, 200 or 300 mm wafers or substrates is straight forward and intuitive. Special designed chucks allowing easy single ICs or wafer fragments loading in the front. Furthermore MPI SmartVacuum™ technology allows automated wafer size or single Die recognition and protects the wafer in case of power interruptions or inexperienced operators from releasing the vacuum inside the IceFreeEnvironment™.


No roll-out stage allows for a simple method of automation for RF calibration and probe card cleaning. Easy access to the AUX chucks for handling of calibration substrates, cleaning or contact check pads.



PROBE PLATEN

Specifications

Material	Nickel plated steel
Chuck top to platen top	Min. 28 mm
Platen cooling	Fully integrated CDA cooling, by using the chiller CDA
Configuration	Probe card holder 4.5 x 11" and/or MicroPositioners
Max. No. of MicroPositioners	10x DC MicroPositioners or 4x DC + 4x HF MicroPositioner Setup
RF MicroPositioner mounting	Magnetic with guided rail
DC MicroPositioner mounting	Magnetic




Large Probe Platen supporting up to 10x DC or 4x DC + 4x RF MicroPositioners or standard 4.5" probe card holder

MICROSCOPE MOVEMENT

XYZ Programmable

XY - Travel range*	50 x 50 mm / 300 x 300 mm
Resolution	1 µm (0.04 mils)
Repeatability	≤ 2 µm (0.08 mils)
Accuracy	≤ 5 µm (0.2 mils)
Z - Travel range	140 mm
Resolution	0.05 µm (0.002 mils)
Repeatability	≤ 2 µm (0.08 mils)
Accuracy	≤ 4 µm (0.16 mils)

*In case of ShieldEnvironment™ X x Y: 25 mm x 25 mm




IceFreeEnvironment™

MPI IceFreeEnvironment™ provides unique capability to perform measurements with probe cards and MicroPositioners simultaneously, especially at negative temperatures down to -60 °C.

Internal node probing with active/passive high impedance probes is very convenient.

The optimized design with minimal tip drop for highest dynamic range and gamma of mmWave and Load Pull measurements make the system an ideal choice for RF/mmW applications on 300 mm wafers.



INTEGRATED CONTROLS

The thermal chuck can be operated by using the fully integrated touchscreen display, placed at convenient location in front of the operator for fast operation and immediate feedback.

The intelligent hardware control panel is completely integrated into the probe system and is designed to provide faster, safer and convenient system control and test operation.

The Keyboard and mouse are strategically located to control the software and it can also control the Windows® based instrumentation.

USB connection to the systems controller is located right in front for convenient data exchange.



Probe Hover Control™

MPI Probe Hover Control PHC™ allows easy manual control of probe contact and separation to wafer. Separation distance can accurately control with micrometer feedback for probe to wafer/pad positioning. Ease of use guarantees the safest operation by minimizing error during critical set-up and probe change operations.




THERMAL CHILLER INTEGRATION

Minimized CDA Consumption

With the ERS patented technology, using the chiller for purging the IceFreeEnvironment™, the CDA consumption is reduced by as much as 50%. Nitrogen purging is also possible by using separate, automated valve.

This “refurbished” CDA is used in addition for probe platen and probe card cooling.



* Picture is courtesyously provided by ERS.

SOFTWARE SOLUTION

MPI automated engineering probe systems are controlled by a unique and revolutionary, multi-touch operation SENTIO® Software Suite – simple and intuitive operation saves significant training time, the Scroll, Zoom, and Move commands mimic modern smart mobile devices and allows everyone to become an expert in just minutes. Switching between the active application and the rest of the APPs is just a matter of a simple finger sweep.

By implementing intuitive multi-touch operation, QAlibria® provides crisp and clear guidance to the RF calibration process, minimizes configuration mistakes and helps to reach accurate calibration results in fastest time. QAlibria® offers industry standard and advanced calibration methods.

QAlibria® includes TOSM (SOLT), TMR, TMRR methods, and 4-port calibration capability additionally to the integration of NIST Statistical calibration packages providing easy access to the NIST multiline TRL metrology-level calibration and uncertain analysis.



NON-THERMAL CHUCKS

Wafer Chuck	Standard	Triaxial
Connectivity	Coax BNC (f)	Kelvin Triax (f)
Diameter	310 mm with 2 integrated AUX areas	
Material	Nickel plated aluminum (flat with 0.5 mm holes)	
Chuck surface	Planar with 0.5 mm diameter holes in centric sections	
Vacuum holes sections (diameter)	4, 24, 48, 72, 96, 120, 144, 168, 192, 216, 240, 264, 288 mm	
SmartVacuum™ distribution	In front for single DUT 5x5 mm (4 holes) and 75 mm (3 in) In center for 150, 200, 300 mm (6, 8, 12 in)	
Surface planarity	$\leq \pm 5 \mu\text{m}^{**}$	
Rigidity	< 15 μm / 10 N @edge	

*Single DUT testing requires higher vacuum conditions dependent upon testing application.

**By using SENTIO® topography

Triaxial RF Wafer Chuck

Connectivity	Kelvin Triax (f)
Diameter	310 mm with 2 integrated AUX chucks
Material	Nickel plated aluminum (flat with 0.5 mm holes)
Chuck surface	Planar with 0.5 mm diameter holes in centric sections
Vacuum holes sections (diameter)	4, 24, 48, 72, 96, 120, 144, 168, 192, 216, 240, 264, 288 mm
SmartVacuum™ distribution	In front for single DUT 5x5 mm (4 holes) and 75 mm (3 in) In center for 150, 200, 300 mm (6, 8, 12 in)
Surface planarity	$\leq \pm 5 \mu\text{m}^{**}$
Rigidity	< 15 μm / 10 N @edge

*Single DUT testing requires higher vacuum conditions dependent upon testing application.

**By using SENTIO® topography

Auxiliary Chuck

Quantity	2 AUX chucks
Position	Integrated to front side of main chuck
Substrate size (W x L)	Max. 25 x 25 mm (1 x 1 in)
Material	Ceramic, RF absorbing material for accurate calibration
Surface planarity	$\leq \pm 5 \mu\text{m}$
Vacuum control	Controlled independently, separate from chucks

Electrical Specification (Coax)

Operation voltage	In accordance with EC 61010, certificates for higher voltages available upon request
Maximum voltage between chuck top and GND	500 V DC
Isolation	> 2 G Ω

Electrical Specification (Triax)

Chuck Isolation	At 10 V
Force-to-Guard	> 5 T Ohm
Guard-to-Shield	> 1 T Ohm
Force-to-Shield	> 5 T Ohm

THERMAL CHUCKS

Specifications of MPI ERS AirCool® PRIME Technology

	Ambient to 200/300 °C	20 °C to 200/300 °C	Ambient to 200/300 °C	20 °C to 200/300 °C
Chuck type	RF	RF	Ultra low noise	Ultra low noise
Connectivity	Kelvin Triax (f)	Kelvin Triax (f)	Kelvin Triax (f)	Kelvin Triax (f)
Temperature control method	Cooling air / Resistance heater	Cooling air / Resistance heater	Cooling air / Resistance heater	Cooling air / Resistance heater
Coolant	Air (user supplied)	Air (user supplied)	Air (user supplied)	Air (user supplied)
Smallest temperature selection step	0.1 °C	0.1 °C	0.1 °C	0.1 °C
Chuck temperature display resolution	0.01 °C	0.01 °C	0.01 °C	0.01 °C
External touchscreen display operation	Yes	Yes	Yes	Yes
Temperature stability	±0.08 °C	±0.08 °C	±0.08 °C	±0.08 °C
Temperature accuracy	±0.1 °C	0.1 °C	0.1 °C	0.1 °C
Control method	Low noise DC/PID	Low noise DC/PID	Low noise DC/PID	Low noise DC/PID
Chuck pinhole surface plating: 200°C / 300°C	Nickel / Gold	Nickel / Gold	Nickel / Gold	Nickel / Gold
SmartVacuum™ distribution	In front for single DUT 5x5 mm (4 holes) and 75 mm (3 in) In center for 150, 200, 300 mm (6, 8, 12 in)			
Temperature sensor	Pt100 1/3DIN, 4-line wired	Pt100 1/3DIN, 4-line wired	Pt100 1/3DIN, 4-line wired	Pt100 1/3DIN, 4-line wired
Temperature uniformity	<±0.5 °C at ≤ 200 °C <±1 °C at > 200 °C	<±0.5 °C at ≤ 200 °C <±1 °C at > 200 °C	<±0.5 °C at ≤ 200 °C <±1 °C at > 200 °C	<±0.5 °C at ≤ 200 °C <±1 °C at > 200 °C
Surface flatness and base parallelism	<±12 µm	<±12 µm	<±12 µm	<±12 µm
Max. Voltage between				
Force-to-GND	600 V DC	600 V DC	600 V DC	600 V DC
Force-to-Guard	100 V DC	100 V DC	600 V DC	600 V DC
Guard-to-GND	400 V DC	400 V DC	400 V DC	400 V DC
Heating rates*	35 to 200 °C < 16 min 35 to 300 °C < 29 min	20 to 200 °C < 19 min 20 to 300 °C < 30 min	35 to 200 °C < 17 min 35 to 300 °C < 33 min	20 to 200 °C < 21 min 20 to 300 °C < 34 min
Cooling rates*	200 to 35 °C < 24 min 300 to 35 °C < 27 min	200 to 20 °C < 35 min 300 to 20 °C < 42 min	200 to 35 °C < 27 min 300 to 35 °C < 31 min	200 to 20 °C < 37 min 300 to 20 °C < 50 min
Leakage @ 10 V	N/A	N/A	< 15 fA at 25 °C < 30 fA at 200 °C < 50 fA at 300 °C	< 15 fA at 25 °C < 30 fA at 200 °C < 50 fA at 300 °C
Electrical isolation	> 5 TΩ at 25 °C > 1 TΩ at 200 °C > 0.5 TΩ at 300 °C	> 5 TΩ at 25 °C > 1 TΩ at 200 °C > 0.5 TΩ at 300 °C	N/A	N/A
Capacitance				
Force-to-Guard	< 1600 pF	< 1600 pF	< 600 pF	< 600 pF
Guard-to-Shield	< 2000 pF	< 2000 pF	< 2000 pF	< 2000 pF

*Typical data for all chucks based on FPS requirements.

Specifications of MPI ERS AirCool® PRIME with Fusion Chiller Technology

	-10 °C to 200/300 °C	-40 °C to 200/300 °C	-60 °C to 200/300 °C
Chuck type	RF	RF	RF
Connectivity	Kelvin Triax (f)	Kelvin Triax (f)	Kelvin Triax (f)
Temperature control method	Cooling air / Resistance heater	Cooling air / Resistance heater	Cooling air / Resistance heater
Coolant	Air (user supplied)	Air (user supplied)	Air (user supplied)
Smallest temperature selection step	0.1 °C	0.1 °C	0.1 °C
Chuck temperature display resolution	0.01 °C	0.01 °C	0.01 °C
External touchscreen display operation	Yes	Yes	Yes
Temperature stability	±0.08 °C	±0.08 °C	±0.08 °C
Temperature accuracy	0.1 °C	0.1 °C	0.1 °C
Control method	Low noise DC/PID	Low noise DC/PID	Low noise DC/PID
Interfaces	RS232C	RS232C	RS232C
Chuck pinhole surface plating: 200°C / 300°C	Nickel / Gold	Nickel / Gold	Nickel / Gold
SmartVacuum™ distribution	In front for single DUT 5x5 mm (4 holes) and 75 mm (3 in) In center for 150, 200 and 300 mm (6, 8, 12 in)		
Temperature sensor	Pt100 1/3DIN, 4-line wired	Pt100 1/3DIN, 4-line wired	Pt100 1/3DIN, 4-line wired
Temperature uniformity	< ±0.5 °C at ≤ 200 °C < ±1 °C at > 200 °C	< ±0.5 °C at ≤ 200 °C < ±1 °C at > 200 °C	< ±0.5 °C at ≤ 200 °C < ±1 °C at > 200 °C
Surface flatness and base parallelism	< ±12 µm	< ±12 µm	< ±12 µm
Max. Voltage between			
Force-to-GND	600 V DC	600 V DC	600 V DC
Force-to-Guard	100 V DC	100 V DC	100 V DC
Guard-to-GND	400 V DC	400 V DC	400 V DC
Heating rates*			
25 °C	-10 to 25 °C < 3 min	-40 to 25 °C < 5 min	-60 to 25 °C < 6 min
200 °C		25 to 200 °C < 16 min	
300 °C		25 to 300 °C < 28 min	
Cooling rates*			
AC3 Mode	300 °C 200 °C 25 °C	300 to 25 °C < 26 min 200 to 25 °C < 21 min 25 to -10 °C < 11 min	300 to 25 °C < 24 min 200 to 25 °C < 22 min 25 to -40 °C < 18 min
TURBO Mode	300 °C 200 °C 25 °C	300 to 25 °C < 26 min 200 to 25 °C < 21 min 25 to -10 °C < 11 min	300 to 25 °C < 23 min 200 to 25 °C < 21 min 25 to -40 °C < 16 min
Leakage @ 10 V	N/A	N/A	N/A
Electrical isolation	> 5 T Ω at 25 °C or below > 1 T Ω at 200 °C, > 0.5 T Ω at 300 °C		
Capacitance			
Force-to-Guard	< 1600 pF	< 1600 pF	< 1600 pF
Guard-to-Shield	< 2000 pF	< 2000 pF	< 2000 pF

*Typical data for all chucks based on FPS requirements.

Specifications of MPI ERS AirCool® PRIME with Fusion Chiller Technology

	-10 °C to 200/300 °C	-40 °C to 200/300 °C	-60 °C to 200/300 °C
Chuck type	Ultra low noise	Ultra low noise	Ultra low noise
Connectivity	Kelvin Triax (f)	Kelvin Triax (f)	Kelvin Triax (f)
Temperature control method	Cooling air / Resistance heater	Cooling air / Resistance heater	Cooling air / Resistance heater
Coolant	Air (user supplied)	Air (user supplied)	Air (user supplied)
Smallest temperature selection step	0.1 °C	0.1 °C	0.1 °C
Chuck temperature display resolution	0.01 °C	0.01 °C	0.01 °C
External touchscreen display operation	Yes	Yes	Yes
Temperature stability	±0.08 °C	±0.08 °C	±0.08 °C
Temperature accuracy	0.1 °C	0.1 °C	0.1 °C
Control method	Low noise DC/PID	Low noise DC/PID	Low noise DC/PID
Interfaces	RS232C	RS232C	RS232C
Chuck pinhole surface plating: 200°C / 300°C	Nickel / Gold	Nickel / Gold	Nickel / Gold
SmartVacuum™ distribution	In front for single DUT 5x5 mm (4 holes) and 75 mm (3 in) In center for 150, 200 and 300 mm (6, 8, 12 in)		
Temperature sensor	Pt100 1/3DIN, 4-line wired	Pt100 1/3DIN, 4-line wired	Pt100 1/3DIN, 4-line wired
Temperature uniformity	<±0.5 °C at ≤ 200 °C <±1 °C at > 200 °C	<±0.5 °C at ≤ 200 °C <±1 °C at > 200 °C	<±0.5 °C at ≤ 200 °C <±1 °C at > 200 °C
Surface flatness and base parallelism	<±12 µm	<±12 µm	<±12 µm
Max. Voltage between			
Force-to-GND	600 V DC	600 V DC	600 V DC
Force-to-Guard	600 V DC	600 V DC	600 V DC
Guard-to-GND	400 V DC	400 V DC	400 V DC
Heating rates*			
25 °C	-10 to 25 °C < 3 min	-40 to 25 °C < 5 min	-60 to 25 °C < 6 min
200 °C		25 to 200 °C < 18 min	
300 °C		25 to 300 °C < 31 min	
Cooling rates*			
AC3 Mode	300 °C	300 to 25 °C < 28 min	300 to 25 °C < 28 min
	200 °C	200 to 25 °C < 23 min	200 to 25 °C < 24 min
	25 °C	25 to -10 °C < 12 min	25 to -40 °C < 20 min
TURBO Mode	300 °C	300 to 25 °C < 28 min	300 to 25 °C < 27 min
	200 °C	200 to 25 °C < 23 min	200 to 25 °C < 23 min
	25 °C	25 to -10 °C < 12 min	25 to -40 °C < 18 min
Leakage @ 10 V			
-10, -40 or -60 °C		< 30 fA	< 30 fA
25 °C		< 15 fA	< 15 fA
200 °C		< 30 fA	< 30 fA
300 °C		< 50 fA	< 50 fA
Capacitance			
Force-to-Guard	< 600 pF	< 600 pF	< 600 pF
Guard-to-Shield	< 2000 pF	< 2000 pF	< 2000 pF

*Typical data for all chucks based on FPS requirements.

High Temperature Uniformity Option*

HTU Option	-60 °C		-50 °C		-35 °C		0 °C	
	typical	max	typical	max	typical	max	typical	max
Accuracy	±0.015	±0.05	±0.015	±0.05	±0.015	±0.05	±0.02	±0.05
Uniformity	±0.4	±0.5	±0.4	±0.5	±0.3	±0.5	±0.15	±0.2
HTU Option	35 °C		50 °C		70 °C			
	typical	max	typical	max	typical	max		
Accuracy	±0.02	±0.05	±0.02	±0.05	±0.025	±0.05		
Uniformity	±0.08	±0.1	±0.08	±0.1	±0.09	±0.1		

* Only for RF thermal chucks.

THERMAL CHUCKS DIMENSIONS**System Controller / Chiller Dimensions and Power / Air Consumption**

System type	W x D x H (mm)	Weight (kg)	Power cons. (VA)	max. Air flow* (l/min)	CDA dew Point
Ambient	300 x 360 x 135	12	1200	400	≤ 0 °C
20 °C, -10 °C to 200 / 300 °C	300 x 360 x 135	12	1200	400	≤ -30 °C
-40 to 200 / 300 °C	420 x 500 x 1020	140	2650	400	≤ -40 °C / -70 °C
-60 to 200 / 300 °C	420 x 500 x 1020	140	2400	450	≤ -40 °C
Electrical primary connection	100 to 240 VAC auto switch				
Electrical frequency	50 Hz / 60 Hz				
Compressed air supply	6.0 bar (0.8 MPa, 87 psi)				



ERS AirCool® Fusion*, Controller Integrated Chiller -40 °C / -60 °C






ERS AirCool® Fusion*, Controller Integrated Chiller -10 °C



ERS and MPI's joint product AirCool® PRIME Chuck won "Electronics Industry Awards 2018" in the category, "Test, Measurement and Inspection Product of the year".

*ERS electronic GmbH patented solution

TYPICAL TRANSITION TIME



SYSTEM CONTROLLER SPECIFICATIONS

CPU	Intel Core i9
RAM	16 GB
64 bit operating system	Windows 11 Enterprise LTSC (English) 64 bit
Storage	500 GB SSD
LAN	1 x internal, 1 x external TCP/IP port
USB Ports	3 x internal, 1 x external
GPIB interface	Optional

SUPPORTED SOFTWARE PLATFORMS

Drivers	WaferPro / IC-CAP & EasyEXPERT from Keysight, BSIMPro & NoisePro from ProPlus, ACS from Keithley
Emulation mode	Available for various prober control software*

*Please contact your local support for more details.

FACILITY REQUIREMENTS

General Probe System

Power	100-240 V AC nominal ; 50/60 Hz
Vacuum	-0.9 bar
Compressed air	6.0 bar

REGULATORY COMPLIANCE

3rd party, TÜV tested according to

- IEC 61010-1: 2010 + Am1:2016; EN 61010-1: 2010; IEC/EN 61010-2-010: 2014; IEC/EN 61010-2-081: 2015; EN ISO 12100: 2010; UL 61010-1: 2012/R: 2016-04; UL 61010-2-010: 2015; CAN/CSA-C22.2 No. 61010-1: 2012/U2: 2016-04; CAN/CSA-C22.2 No. 61010-2-010:2015

and certified for CE and US/Canada (NRTL), SEMI S2 and S8.

Copies of certificates are available on request

WARRANTY

- Warranty*: 12 months
- Extended service contract: contact MPI Corporation for more information

*See MPI Corporation's *Terms and Conditions of Sale* for more details.




PHYSICAL DIMENSIONS

TS3500-IFE

System dimensions (W x D x H) 1400 x 1315 x 1600 mm (55.1 x 51.8 x 63.0 in)

Weight 850 kg




*Can vary depends on monitor/chiller position.



WaferWallet®

System dimensions (W x D x H)	500 x 1265 x 970 mm (19.7 x 49.8 x 38.2 in)
Weight	180 kg


*Can vary depends on monitor/chiller position.

TS3500-IFE with WaferWallet®

WaferWallet®MAX

System dimensions (W x D x H)	530 x 1300 x 970 mm (20.9 x 51.2 x 38.2 in)
Weight	200 kg

*Can vary depends on monitor/chiller position.




TS3500-IFE with WaferWallet®MAX

WaferWallet®ULTRA

System dimensions (W x D x H) 600 x 1660 x 2040 mm (23.6 x 65.4 x 80.3 in)

Weight* 328 kg

*Can vary depends on the optional accessories.

TS3500-IFE with WaferWallet®ULTRA

*Can vary depends on monitor/chiller position.

MPI global presence: for your local support, please find the right contact here:
mpi-corporation.com/ast/support/regional-sales-contact

© 2025 Copyright MPI Corporation. All rights reserved.

MPI Global Presence

Direct contact:
 Asia region: ast-asia@mpi-corporation.com
 EMEA region: ast-europe@mpi-corporation.com
 America region: ast-americas@mpi-corporation.com

